


Product dimension(0805)

Recommended Pad Layout (mm)

Model	A		B		C		D
	Min.	Max.	Min.	Max.	Min.	Max.	Min.
PPSM010	2.00	2.20	1.20	1.50	0.55	0.95	0.20
PPSM020	2.00	2.20	1.20	1.50	0.55	0.95	0.20
PPSM035	2.00	2.20	1.20	1.50	0.40	0.80	0.20
PPSM050	2.00	2.20	1.20	1.50	0.40	0.80	0.20
PPSM075	2.00	2.20	1.20	1.50	0.75	1.25	0.20
PPSM100	2.00	2.20	1.20	1.50	0.75	1.25	0.20
PPSM110	2.00	2.20	1.20	1.50	0.75	1.25	0.20